



- ▶ Suited for reverberant environments
- ▶ 90° Uniform Horizontal Coverage
- ▶ 400W Program
- ▶ Elegant and visually discreet design
- ▶ Rigid fiberglass enclosure
- ▶ Low and High impedance

## Technical Specifications

<b>LF Transducers:</b>	1 x 8" Diameter, 2" Voice coil speaker
<b>HF Transducers:</b>	1 x 1" Exit, 1" Voice coil compression driver
<b>Nominal Impedance:</b>	8 ohm
<b>LF Minimum Impedance</b>	6.6 ohm @ 200 Hz
<b>RMS Power<sup>(1)</sup>:</b>	200W
<b>Program Power<sup>(2)</sup>:</b>	400W
<b>Peak Power<sup>(3)</sup>:</b>	800W
<b>Transformer:</b>	60W @ 100V, 30W @ 70V
<b>Sensitivity (2.83v @ 1m):</b>	95 dB SPL
<b>Peak SPL<sup>(4)</sup>:</b>	123 dB SPL
<b>Frequency Range (Full Space)<sup>(5)</sup>:</b>	61Hz to 19kHz (-10dB) 72Hz to 17kHz (-6dB)
<b>Recommended High Pass Filter:</b>	Butterworth 24dB/Oct, 35Hz
<b>Coverage (-6dB)</b>	90°
<b>Enclosure:</b>	High quality fiberglass
<b>Grille:</b>	Steel grille, foam backing
<b>Connector:</b>	Two poles Euroblock
<b>Color:</b>	Black or white.
<b>Rigging:</b>	One rigging point built-in steel hardware.
<b>Dimensions (HxWxD):</b>	364x289x289 mm, 14.3x11.4x11.4 in
<b>Net Weight:</b>	9kg, 19.8 lb
<b>Included accessories:</b>	CS 10 E is a 5m (16.4 foot) long, 2mm diameter steel cable. Two units are included, one to be used as main rigging cable and one as safety cable.
<b>Optional accessory:</b>	TP8 is a top cover in wood finish or customized color under request.

(1) Based on a 2h power test run with pink noise, 6dB crest factor, IEC filtered

(2) Conventionally, 3dB higher than the RMS Power

(3) Corresponds to the crest factor for the test described in 1

(4) Calculated based on peak Power and sensitivity

(5) Free Field

## Overview

The SN8 is a high output, full range, passive, two-way coaxial pendant loudspeaker which provides voice intelligibility and musical clarity in acoustically challenging environments such as shopping malls, houses of worship, restaurants, congress halls, hotels, airports, train stations, swimming pools, conference rooms or museums, where high ceiling structures create a reverberant sound field.


Each unit features one 8" transducer, 2" voice coil, in a bass reflex enclosure for the low frequencies, with optimized dual ports. The high frequencies are reproduced by a coaxially mounted 1" diameter voice coil compression driver featuring a polymer membrane and ferrofluid cooling which contributes to an improved efficiency and lower power compression. It is coupled to a horn device which provides a consistent 90° symmetric coverage over the vocal range.

The screwless, one single piece enclosure has been designed for a seamless visual integration in every venue, and is made of rigid, high quality black or white fiberglass. The steel grille is magnetically attached to avoid the use of screws, and includes a steel safety wire to prevent it from a falling hazard. A single point hanging hardware, concealed under a top cover for clean appearance, is included on the cabinet for fast and secure suspension, featuring two additional spare holes for safety cables.

The system includes a two poles Euroblock connector. A two positions switch allows for low and high impedance connections of the SN8, which houses a high quality 60Wrms transformer that makes it suitable for installations where long cables have to be deployed.

Tuning presets are available to enhance the frequency balance and intelligibility.


## Dimensions



All dimensions in mm


**Frequency Response**

On axis frequency response of one SN8 unit driven by a swept sine wave signal at an input level of 2.83v. Measured in an anechoic chamber at 3m, SPL scaled down to 1m. In order to provide a more detailed frequency response curve only a 1/6th octave smoothing has been applied. Black Dashed: No EQ. Black Solid: With recommended preset "SN8\_F1V1". Grey Dashed: With recommended preset SN8\_Sh+3dBV1"



**Impedance**

Impedance curve of one SN8 unit measured with a swept sine wave signal. Frequency resolution is 1/24th octave. In order to provide better resolution at lower impedance values a logarithmic vertical scale has been used.



**1/3 Octave Polar Response**

