



- ▶ Suited for reverberant environments
- ▶ 90° Uniform Horizontal Coverage
- ▶ 400W Program
- ▶ Elegant and visually discreet design
- ▶ Paintable, rigid fiberglass enclosure
- ▶ Low and High impedance

Technical Specifications

LF Transducers:	1 x 8" Diameter, 2" Voice coil speaker
HF Transducers:	1 x 1" Exit, 1" Voice coil compression driver
Nominal Impedance:	8 ohm
LF Minimum Impedance	6.6 ohm @ 200 Hz
RMS Power⁽¹⁾:	200W
Program Power⁽²⁾:	400W
Peak Power⁽³⁾:	800W
Transformer:	60W @ 100V, 35W @ 70V
Sensitivity (2.83v @ 1m):	95 dB SPL
Peak SPL⁽⁴⁾:	123 dB SPL
Frequency Range (Full Space)⁽⁵⁾:	61Hz to 19kHz (-10dB) 72Hz to 17kHz (-6dB) Butterworth 24dB/Oct, 35Hz
Recommended High Pass Filter:	
Coverage (-6dB)	90°
IP Rating:	IP65
Enclosure:	Paintable high quality fiberglass
Grille:	Steel grille, foam backing
Connector:	Four pole stripped wire. Low Z: Red(+) & Black(-). Yellow(NC) & Green (NC). High Z: Red & Green (Linked), Yellow(+) Black(-). Black or white.
Color:	Black or white.
Rigging:	Three rigging points built-in steel hardware.
Dimensions (HxWxD):	364x289x289 mm, 14.3x11.4x11.4 in
Net Weight:	9kg, 19.8 lb
Included accessories:	One 4.5m (15 foot) long, 2mm diameter, main rigging steel cable and one 4.5m (15 foot) long, 2mm diameter, safety steel cable.
Optional accessories:	Top cover in wood finish (TP8) or customized color under request.

(1) Based on a 2h power test run with pink noise, 6dB crest factor, IEC filtered

(2) Conventionally, 3dB higher than the RMS Power

(3) Corresponds to the crest factor for the test described in 1

(4) Calculated based on peak Power and sensitivity

(5) Free Field

Overview

The SN8 is a high output, full range, passive, two-way coaxial pendant loudspeaker which provides voice intelligibility and musical clarity in acoustically challenging environments such as shopping malls, houses of worship, restaurants, congress halls, hotels, airports, train stations, swimming pools, conference rooms or museums, where high ceiling structures create a reverberant sound field.

Each unit features one 8" transducer, 2" voice coil, in a bass reflex enclosure for the low frequencies, with optimized dual ports. The high frequencies are reproduced by a coaxially mounted 1" diameter voice coil compression driver featuring a polymer membrane and ferrofluid cooling which contributes to an improved efficiency and lower power compression. It is coupled to a horn device which provides a consistent 90° symetric coverage over the vocal range.


The screwless, one single piece enclosure has been designed for a seamless visual integration in every venue, and is made of paintable, rigid, high quality black or white fiberglass. The steel grille is magnetically attached to avoid the use of screws, and includes a steel safety wire to prevent it from a falling hazard. A single point hanging hardware, concealed under a top cover for clean appearance, is included on the cabinet for fast and secure suspension, featuring two additional spare holes for safety cables.

The system also includes 2m of four poles electrical connection cable, which enters the enclosure through a cable gland preventing thereby water, dust or moisture from damaging the transducers.

The four stripped wires cable allow for low and high impedance connections of the SN8, which houses a high quality 60Wrms transformer that makes it suitable for installations where long cables have to be deployed.

Tuning presets are available to enhance the frequency balance and intelligibility.


Dimensions



All dimensions in mm


Frequency Response

On axis frequency response of one SN8 unit driven by a swept sine wave signal at an input level of 2.83v. Measured in an anechoic chamber at 3m, SPL scaled down to 1m. In order to provide a more detailed frequency response curve only a 1/6th octave smoothing has been applied. Black Solid: No EQ. Grey Dashed: With recommended preset "SN8F1V1".



Impedance

Impedance curve of one SN8 unit measured with a swept sine wave signal. Frequency resolution is 1/24th octave. In order to provide better resolution at lower impedance values a logarithmic vertical scale has been used.



1/3 Octave Polar Response

