







VESA Compatible:	Max 680 x 480
Weight Capacity:	40kgs
Lifting Range:	800-1700mm
Rotation:	90°
Column segments:	1


IMPORTANT SAFETY INSTRUCTIONS

Please read through these instructions completely to be sure you're comfortable with this easy install process. Also check your Monitor owner's manual to see if there are any special requirements for mounting your Monitor. If you do not understand these instructions or have doubts about the safety of the installation, assembly or use of this product, contact your Customer Service.


Parts for assembly



Hardware




1.1



Assembly the cart



2.1


Loosen the screws at the bottom of the column and remove the plate



Assemble the column and base

2.2





VESA Compatible	Max 680 x 480
Peso soportado	40kgs
Elevación	800-1700mm
Rotación:	90°
Columnas	1




INSTRUCCIONES IMPORTANTES DE SEGURIDAD

Lea estas instrucciones completamente para familiarizarse con este proceso de fácil instalación.


Compruebe el manual de su monitor para ver si precisa algún requerimiento especial para su montaje.

Si no comprende estas instrucciones o tiene dudas sobre la seguridad de su instalación, montaje o uso de este producto, contacte con su distribuidor


Elementos de montaje



Hardware




1.1



Montaje del carro

2.1

Afloje los tornillos de la parte inferior de la columna y retire la placa



Monte la columna y la base

2.2

